

Dehydrator and Accessory Products

Type Number	Description
40525B	Manual Regenerative Dehydrator 120V/60
40525B-3	Manual Regenerative Dehydrator 230V/50
40525B-4	Manual Regenerative Dehydrator 120V/60
40525B-5	Manual Regenerative Dehydrator 220V/50
MT050A-81015	Dehydrator, 115/220 VAC 50/60 Hz,. Factory set at 5 psi.
MT050A-81315	Dehydrator, 115/220 VAC 50/60 Hz,, 5 PSI, ALARMS HH,LP,XR,PF US cord
MT300-81015	Dehydrator 115 VAC 60 Hz, no sound deadening 3-8 PSI .3 CFM Low Pressure alarm
MT300-81026	Dehydrator 220V50/60Hz no sound deadening 3-8 PSI .3 CFM Low Pressure alarm
MT300-82015	Dehydrator 115 VAC 60 Hz, sound deadening 3-8 PSI .3 CFM Low Pressure alarm
MT300-82026	Dehydrator 220V50/60Hz sound deadening 3-8 PSI .3 CFM Low Pressure alarm
MT300-81315	Dehydrator 115 VAC 60 Hz, no sound deadening Excessive Run High Humidity alarms 3-8 PSI
MT300-81326	Dehydrator 220V50/60Hz no sound deadening Excessive Run High Humidity alarms 3-8 PSI
MT300-82315	Dehydrator 115 VAC 60 Hz, sound deadening 3-8 PSI Excessive Run High Humidity alarms
MT300-82326	Dehydrator 220V50/60Hz sound deadening 3-8 PSI Excessive Run High Humidity alarms
PMT200A-82015	Dehydrator, Wall Mount, Regulated 5 lb/in ² , Low Pressure, Excess Run and Power Fail alarms output via a summary alarm, 115/230 VAC, 50/60 Hz, Auto-detecting, USA/Europe power cords.
PMT200A-82315	Dehydrator, Wall Mount, Regulated 5 lb/in ² , Low Pressure, PWR Fail, High Humidity and Excess Run alarms output through discrete relays. 115/230 VAC, 50/60 Hz, Auto-detecting, USA/Europe power cords.
MT1000-32325	Dehydrator, MT1000, 1-4 PSI, 230 VAC, 50/60 Hz, UL/CSA cord with 6-15P plug
MT1000-32326	Dehydrator, MT1000, 1-4 PSI, 230 VAC, 50/60 Hz, CE harmonized cord
MT2000-32325	Dehydrator, MT2000, 1-4 PSI, 230 VAC, 50/60 Hz, UL/CSA cord with 6-15P plug
MT2000-32326	Dehydrator, MT2000, 1-4 PSI, 230 VAC, 50/60 Hz, CE harmonized cord
XT1000-92325	Dehydrator, XT1000, 0.3-5 PSI, 230V, UL/CSA cord with 6-15P plug
XT1000-92326	Dehydrator, XT1000, 0.3-5 PSI, 230V, CE harmonized cord
NXT1000-92325	Dehydrator, NXT1000, 0.3-5 PSI, 230V, UL/CSA cord with 6-15P plug
NXT1000-92326	Dehydrator, NXT1000, 0.3-5 PSI, 230V, UL/CSA cord with 6-15P plug
XT2000-92325	Dehydrator, XT2000, 0.3-5 PSI, 230V, UL/CSA cord with 6-15P plug
XT2000-92326	Dehydrator, XT2000, 0.3-5 PSI, 230V, CE harmonized cord
NXT2000-92325	Dehydrator, NXT2000, 0.3-5 PSI, 230V, UL/CSA cord with 6-15P plug
XT4500-91325	Dehydrator, XT4500, 0.3-5 PSI, 230V, US cord
6600D-2	Two outlet gas manifold with gauge and shutoff valve includes 3/8 tube installation kit
6600D-4	Four outlet gas manifold with gauge and shutoff valve includes 3/8 tube installation kit
6600D-6	Six outlet gas manifold with gauge and shutoff valve includes 3/8 tube installation kit
858C	Nitrogen Tank Regulator Adjustable (0-15 Psig) With High And Low Gauges And 3/8 Tube Installation Kit (CGA580 connection)
RLAPBK-1	Pressurization Bypass Kit, 1 foot
RLAPBK-2	Pressurization Bypass Kit, 2 foot
RLAPBK-3	Pressurization Bypass Kit, 3 foot
RLAPBK-4	Pressurization Bypass Kit, 4 foot with pressure gauge.